

**1,6 mm crimp contact f/turned/gold/0,75-1 mm<sup>2</sup>**

100 pieces

Turned crimp contact

Female

1.6 mm

0.75...1 mm<sup>2</sup> (AWG 18)

Quantity: 100 pcs.

Technical data will be only guaranteed with Murrelektronik components.

**Link to Product****Illustration**

Product may differ from Image

**classifications**

ECLASS-6.0	27143424
ECLASS-7.0	27440209
ECLASS-8.0	27440209
ECLASS-9.0	27440209
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796

**Technical Data**

Mating cycles	min. 500
Connection	Crimp
Connection cross section	0.75...1 mm <sup>2</sup> (AWG 18)
Stripping length	7 mm

**General data**

Material contact	Brass
Material contact surface	Au
Type	Female
Dimensions H×W×D	3.5×3.5×21.6 mm

**Commercial data**

customs tariff number	85366990
GTIN	4048879653589
Packaging unit	100