

2,5 mm crimp contact f/turned/silver/4 mm²

100 pieces

Turned crimp contact

Female

2.5 mm

4 mm² (AWG 12)

Quantity: 100 pcs.

Technical data will be only guaranteed with Murrelektronik components.

[Link to Product](#)**Illustration**

Product may differ from Image

Commercial data

ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
GTIN	4048879653657
Packaging unit	100

Installation

Connection cross section max.	4 mm ²
AWG number max.	12

Installation | Connection

Stripping length	6,5 mm
Connection	Crimp
Gender	female
Mating cycles min.	500

Mechanical data | Material data

Coating contact	silver-plated
-----------------	---------------

Brass

Height	4,5 mm
Width	4,5 mm
Depth	22 mm

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com