

**SIEMENS CONTACTOR SUPPRESSOR**

RC, 24VDC


24 V AC/DC

RC

For other configurations and voltages, please inquire.

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27371013
ECLASS-6.1	27371013
ECLASS-7.0	27371013
ECLASS-8.0	27371013
ECLASS-9.0	27371013
ECLASS-10.1	27371013

ECLASS-11.1	27371013
ECLASS-12.0	27371013
ETIM-5.0	EC002498
customs tariff number	85363010
GTIN	4048879019965
Packaging unit	1

**Compatibility | Compatible with**

Appropriate contactors	3 RT 10.24/25/26
------------------------	------------------

**Electrical data | Input**

Input voltage AC min.	24 V
Input voltage AC max.	70 V
Input voltage DC min.	24 V
Input voltage DC max.	70 V

**Mechanical data | Mounting data**

Height	36 mm
Width	36 mm
Depth	10,2 mm

**Environmental characteristics | Climatic**

Operating temperature min.	-20 °C
Operating temperature max.	70 °C