

POWER DISTRIBUTOR PD4 PLUG 24+E

Connector for 27680 and 27681

Industry female plug 24+PE
Field-wireable

[Link to Product](#)

Illustration



Product may differ from Image



| Commercial data | |
|--|-------------------|
| ECLASS-6.0 | 27279219 |
| ECLASS-6.1 | 27142601 |
| ECLASS-7.0 | 27142601 |
| ECLASS-8.0 | 27142601 |
| ECLASS-9.0 | 27142601 |
| ECLASS-10.1 | 27142601 |
| ECLASS-11.1 | 27142606 |
| ECLASS-12.0 | 27142606 |
| ETIM-5.0 | EC002585 |
| customs tariff number | 85366990 |
| GTIN | 4048879063432 |
| Packaging unit | 1 |
| Electrical data | |
| Security level | SELV |
| Electrical data Supply | |
| Operating voltage AC | 50 V |
| Operating voltage DC | 120 V |
| Current operating per contact max. | 9 A |
| Device protection Electrical | |
| Degree of protection (EN IEC 60529) | IP67 |
| Additional condition protection degree | inserted, screwed |

Mechanical data | Material data

| | |
|------------------|----------------------|
| Coating housing | powder-coated |
| Material housing | Aluminum die casting |

Mechanical data | Mounting data

| | |
|---------------------|--------|
| Clamping range min. | 9 mm |
| Clamping range max. | 17 mm |
| Height | 120 mm |
| Width | 43 mm |
| Depth | 70 mm |

Environmental characteristics | Climatic

| | |
|----------------------------|--------|
| Operating temperature min. | -30 °C |
| Operating temperature max. | 85 °C |