

UFL 10 L PLUG FOR SIGNAL TRANSFER

24 VDC / 1 A - male with LED

Ribbon cable connector + LED

10-pole

Via the combined fixing mechanism, connectors with or without strain relief can be connected.  
for plugs with or without strain relief (DIN 41651); for plugs with strain relief, it may be necessary to remove the bottom hook

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27141120
ECLASS-6.1	27141120
ECLASS-7.0	27141120
ECLASS-8.0	27141120
ECLASS-9.0	27141120

ECLASS-10.1	27141120
ECLASS-11.1	27141120
ECLASS-12.0	27141120
ETIM-5.0	EC001283
customs tariff number	85366990
GTIN	4048879026611
Packaging unit	1

**Electrical data | Supply**

Operating voltage AC	24 V
Operating current max.	1 A

**Diagnostics**

Status indication LED	red
-----------------------	-----

**Device protection | Electrical**

Overvoltage category (EN 60664-1)	II
-----------------------------------	----

**Mechanical data | Mounting data**

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	63 mm
Width	50 mm
Depth	48 mm

**Environmental characteristics | Climatic**

Operating temperature min.	-20 °C
Operating temperature max.	70 °C