

PROFIBUS-PLUG-MALE (SUB-D) 180°

Cut clamp for rigid and flexible wires

Bus connection plug 180°  
PROFIBUS  
SUB-D9 (male), IDC terminals, rigid and flexible cable, programming device connection  
PROFIBUS, FC cable rigid/flexible, 1× 2× 0.64 mm², for outer diameter 8.0 ±0.5 mm

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27242692
ECLASS-11.1	27242692
ECLASS-12.0	27242692
ETIM-5.0	EC001855
customs tariff number	85389091
GTIN	4048879050579
Packaging unit	1
Electrical data	
Terminating resistor	connectable, integrated
Electrical data   Supply	
Operating voltage DC min.	4,75 V
Operating voltage DC max.	5,25 V
Current consumption max.	12,5 mA
Industrial communication	
Data transmission rate max.	12 MBit/s
Installation   Connection	

The information in this Product-PDF has been compiled with the utmost care.  
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-04-28

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | [shop@murrinc.com](mailto:shop@murrinc.com) | [shop.murrinc.com](http://shop.murrinc.com)