

CUBE20 POTENTIAL TERMINAL BLOCK 4xBROWN

Potential terminal block

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27141106
ECLASS-7.0	27141106
ECLASS-8.0	27141106
ECLASS-9.0	27141106
ETIM-5.0	EC001283
customs tariff number	85369010
GTIN	4048879567459
Packaging unit	1
Electrical data Supply	
Operating voltage AC max.	30 V
Operating voltage DC max.	30 V
Total current max.	10 A
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data Mounting data	
Height	70 mm
Width	56 mm
Depth	32,5 mm
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C
Connection type 1	

Connection type 1	X3
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	colorless
No. of poles	10
PIN 1	24 V DC
PIN 2	24 V DC
PIN 3	24 V DC
PIN 4	24 V DC
PIN 5	24 V DC
PIN 6	24 V DC
PIN 7	24 V DC
PIN 8	24 V DC
PIN 9	24 V DC
PIN 10	24 V DC