

Cube67 Valve-Interface, I/O Extension Module

DO32, MAC Valves, D-Sub HD44F 44 pol.,


Expansion module
Cube67 DO32 E - Valve
Multipole plug (0.5 A)
MAC - SUB-D44
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ECLASS-10.1	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ETIM-5.0	EC001599
customs tariff number	85389099
GTIN	4048879048361
Packaging unit	1
Electrical data Supply	
Norm operating voltage	EN 61131-2
Operating voltage UA DC	24 V
Current consumption max.	50 mA
Total current UA max.	4 A
Total current US max.	4 A
Electrical data Output	

Overload resistant	yes
Short-circuit protected	yes
Output current per pin max.	0,5 A

Diagnostics

Actuator warning	per channel via BUS
Diagnostic	No voltage, Under voltage
Diagnostic via BUS	per module and channel
Diagnostic via LED	per module
Short circuit diagnosis	yes
LED display	Ethernet connection/data traffic
Overload diagnosis	yes

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
-------------------------------------	------

Mechanical data | Mounting data

Suitable for mounting type	2-hole screw mounting
Height	124 mm
Width	36 mm
Depth	39,5 mm

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-20 °C
Storage temperature max.	70 °C

Connection type 2

Connection type 1	Bus Out
Connection type 2	Data
Family construction form	M12
Gender	male
Color contact carrier	black
Coding	A
No. of poles	6
PIN 1	24 V DC (UA)
PIN 2	24 V DC (US)
PIN 3	0 V
PIN 4	Bus internal
PIN 5	Bus internal
PIN 6	0 V
Family construction form	D-Sub
Gender	female
No. of poles	44
PIN 1	Out 0
PIN 2	Out 1
PIN 3	Out 2
PIN 4	Out 3
PIN 5	Out 4
PIN 6	Out 5
PIN 7	Out 6
PIN 8	Out 7
PIN 9	Out 8
PIN 10	Out 9
PIN 11	Out 10
PIN 12	Out 11

PIN 13	Out 12
PIN 14	Out 13
PIN 15	Out 14
PIN 16	Out 15
PIN 17	Out 16
PIN 18	Out 17
PIN 19	Out 18
PIN 20	Out 19
PIN 21	Out 20
PIN 22	Out 21
PIN 23	Out 22
PIN 24	Out 23
PIN 25	Out 24
PIN 26	Out 25
PIN 27	Out 26
PIN 28	Out 27
PIN 29	Out 28
PIN 30	Out 29
PIN 31	Out 30
PIN 32	Out 31
PIN 33	Sens
PIN 34	0 V
PIN 35	0 V
PIN 36	0 V
PIN 37	0 V
PIN 38	0 V
PIN 39	0 V
PIN 40	0 V
PIN 41	0 V
PIN 42	0 V
PIN 43	FE
PIN 44	FE