

MIRO BT

IP65 Bluetooth Master/Slave PROFINET


PROFINET
Bluetooth Master/Slave
100 Mbit/s
Connection cables are in the online shop under "Connection Technology".

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	19170101
ECLASS-6.1	27242602
ECLASS-7.0	27242602
ECLASS-8.0	27242602
ECLASS-9.0	27242602
ECLASS-10.1	27242602
ECLASS-11.1	27242602
ECLASS-12.0	27242602
ETIM-5.0	EC001604
ETIM-6.0	EC001604
ETIM-7.0	EC001604
customs tariff number	85176200
GTIN	4048879582414
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Operating current max.	150 mA
Industrial communication	
Radio frequency	2.4 GHz Bluetooth
Transmission power	100 mW

Installation Connection	
Antenna connection	SMA-female (50 Ω)
Mounting set	M4
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Mechanical data Material data	
Color housing	black
Material housing	Metal
Mechanical data Mounting data	
Mounting method	screwed
Height	125 mm
Width	86 mm
Depth	41 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Storage temperature min.	-40 °C
Storage temperature max.	75 °C
Conformity	
Product standard	EN 61131-2
Connection type 4	
Connection type 1	10M / 100M
Connection type 2	24 V DC
Connection type 3	Ant
Family construction form	M12
Gender	female
Color contact carrier	green
Coding	D
No. of poles	4
PIN 1	TD +
PIN 2	RD +
PIN 3	TD -
PIN 4	RD -
Family construction form	M12
Gender	male
Color contact carrier	black
Coding	A
No. of poles	5
PIN 1	25 V DC
PIN 3	0 V
PIN 5	PE
Family construction form	SMA
Gender	female
No. of poles	2
PIN 1	Signal
PIN 2	PE
Family construction form	USB Mini
Gender	female
No. of poles	5