

Xenterra 16TX unmanaged Switch wallmounted 16 Port 100Mbit


16 port unmanaged switch  
Key-hole mounting/screwable  
Connection cables are in the online shop under "Connection Technology".

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.1	19170106
ECLASS-7.0	19170106
ECLASS-8.0	19170106
ECLASS-9.0	19170402
ECLASS-10.1	19170402
ECLASS-11.1	19170402
ECLASS-12.0	19170402
customs tariff number	85176200
GTIN	4048879830430
Packaging unit	1
Electrical data   Supply	
Operating voltage AC min.	8 V
Operating voltage AC max.	28 V
Operating voltage DC min.	9 V
Operating voltage DC max.	36 V
Industrial communication	
Data transmission rate max.	100 MBit/s
Industrial communication   Ethernet functionality	
Auto-crossover	yes
Auto-negotiation	yes
duplex	Full duplex
Switch type	unmanaged

VLAN unmanaged (IEEE 802.1Q)      yes

#### Diagnostics

Alarm contact      no

Diagnostic      No voltage

LED display      Ethernet connection/data traffic

#### Device protection | Electrical

Degree of protection (EN IEC 60529)      IP20

#### Mechanical data | Material data

Color housing      black

Material housing      Metal

#### Mechanical data | Mounting data

Mounting method      screwed

Suitable for mounting type      Schlüssellochabhängung

Height      105 mm

Width      137 mm

Depth      28 mm

#### Environmental characteristics | Climatic

Operating temperature min.      -40 °C

Operating temperature max.      70 °C

Storage temperature min.      -40 °C

Storage temperature max.      85 °C

#### Connection type 1

Connection type 1      16

Family construction form      RJ45

Gender      female

Color contact carrier      black

No. of poles      8

PIN 1      TD +

PIN 2      TD -

PIN 3      RD +

PIN 4      n.c.

PIN 5      n.c.

PIN 6      RD -

PIN 7      n.c.

PIN 8      n.c.