



INDUSTRIAL RELAYS 4W 24VDC + DIODE

Product discontinued, no alternative

4 NO/NC contacts  
24 V DC, with suppressor and LED  
Relays with other voltage available on request.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27371001
ECLASS-7.0	27371001
ECLASS-8.0	27371001
ECLASS-9.0	27371001
ETIM-5.0	EC001437
customs tariff number	85364900
GTIN	4048879025720
Packaging unit	1
Electrical data	
Holding power max.	0,9 W
Electrical data   Output	

Power rating AC max.	1250 VA
----------------------	---------

Power rating DC max.	100 W
----------------------	-------

Switching voltage AC max.	250 V
---------------------------	-------

Switching voltage DC	24 V
----------------------	------

Switching voltage DC max.	110 V
---------------------------	-------

Switching current max.	5 A
------------------------	-----

**Mechanical data | Material data**

Material contact	AgHv, AgNi
------------------	------------

**Mechanical data | Mounting data**

Height	36 mm
--------	-------

Width	28 mm
-------	-------

Depth	21 mm
-------	-------