

LED - LT 24/GREEN

(green)  
24 V DC  
with lamp test input  
The modules are suitable for wall thickness of 1.5...5.0 mm.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27261590
ECLASS-6.1	27261501
ECLASS-7.0	27261501
ECLASS-8.0	27261501
ECLASS-9.0	27261501
ECLASS-10.1	27261501
ECLASS-11.1	27261501
ECLASS-12.0	27261501
ETIM-5.0	EC000272
customs tariff number	85318070
GTIN	4048879041225
Packaging unit	10
Electrical data   Supply	
Operating voltage DC	24 V
Operating voltage DC min.	20,4 V
Operating voltage DC max.	26,4 V
Current consumption max.	10 mA
Installation   Connection	
Connection information	Faston 2.8×0.8 mm
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP65
Device protection   Media	
Flame resistance	flame retardant
Mechanical data	
Diameter LED	5 mm

**Mechanical data | Material data**

Material housing	Plastic
------------------	---------

**Mechanical data | Mounting data**

Diameter front panel drilling	9 mm
-------------------------------	------

**Environmental characteristics | Climatic**

Operating temperature min.	-20 °C
Operating temperature max.	50 °C