


MPL POWER SUPPLY 3-PHASE, SMOOTHED

IN: 400VAC+/- 5% OUT: 24V/15ADC

Current: 15 A
Output rating: 360 W
This power supply units meet the (EN 61000-3-2) standard for harmonic current.
Any mounting position on vertical wall, condensation not permissible

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040701
ECLASS-10.1	27040701

ECLASS-11.1	27040701
ECLASS-12.0	27040701
ETIM-5.0	EC002540
customs tariff number	85044095
GTIN	4048879079235
Packaging unit	1
Electrical data	
Security level	SELV
Electrical data Supply	
Power frequency	50 ... 60 Hz
Electrical data Input	
Fuse protection 1 primary side external	1 A
Characteristic back-up fuse	Inertia
Input voltage AC	400 V
Input voltage AC min.	380 V
Input voltage AC max.	420 V
Input current AC (3-phase)	0,8 A
Phase number input	3
Efficiency	77 %
Electrical data Output	
Fuse protection secondary side external	15 A
Output suppression	LED, Screening capacitor, VDR
Output voltage DC	24 V
Output voltage adjustable	no
Output current max.	15 A
Characteristic secondary fuse	Inertia
Ripple max.	2 %
Mechanical data Mounting data	
Suitable for mounting type	Schlüssellochabhängung
Mounting dimension a	195 mm
Mounting dimension b	59 mm
Mounting dimension c	6,5 mm
Height	220 mm
Width	81 mm
Depth	210 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	55 °C
Conformity	
Product standard	EN 61558-2-6, EN 62041 category I
EMC	EN 55011 B, EN 61000-3-2