

EUROCARD HOLDER

SKPD form D, 230V, 32-pole, 234x160mm

screw terminal
32-pole
230 V AC

To insert the card first press down the 2 yellow buttons. Then slide the Eurocard into the guide slots pushing until fully engaged. The card is now locked into position. It can be removed by pressing down on the 2 yellow buttons.

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27260710
ECLASS-6.1	27260704
ECLASS-7.0	27440402
ECLASS-8.0	27440402
ECLASS-9.0	27440402
ECLASS-10.1	27440402
ECLASS-11.1	27460201
ECLASS-12.0	27460201
ETIM-5.0	EC002780
customs tariff number	85366990
GTIN	4048879040051
Packaging unit	1
Electrical data Supply	
Operating voltage AC	230 V
Operating current max.	4 A
Installation	
Connection cross-section solid min.	0,25 mm²
Connection cross-section solid max.	4 mm²
Connection cross-section stranded/fine-stranded min.	0,5 mm²

Connection cross-section stranded/fine-stranded max. 2,5 mm²

Installation | Connection

Connection Screw terminals SK

Installation | Pin assignment

No. of poles 32

Device protection | Media

Flame resistance flame retardant

Mechanical data | Material data

Material housing Plastic

Mechanical data | Mounting data

Mounting method	screwed
Suitable for mounting type	mounting rail
Height	63 mm
Width	274 mm
Depth	167 mm