



MET SINGLE-PHASE CONTROL AND ISOLATION TRANSFORMER

P:500VA IN:400VAC±5% OUT:110VAC

Single-phase - Control and Isolation Transformers
500 VA
Isolation class T 40/B

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27031202
ECLASS-6.1	27031302
ECLASS-7.0	27031302
ECLASS-8.0	27031302
ECLASS-9.0	27031302
ECLASS-10.1	27031302

ECLASS-11.1	27031302
ECLASS-12.0	27031302
ETIM-5.0	EC002485
customs tariff number	85043180
GTIN	4048879073882
Packaging unit	1
Electrical data Supply	
Power frequency	50 ... 60 Hz
Electrical data Input	
Input voltage AC	400 V
Input voltage AC min.	380 V
Input voltage AC max.	420 V
Current input AC	2,67 A
Max. inrush current	23 A
Short-circuit current	31 A
Electrical data Output	
Output voltage AC 1	110 V
Output voltage adjustable	no
Power rating AC max.	500 VA
Device protection Electrical	
Insulation test voltage input - output	5,8 kV
Mechanical data Mounting data	
Mounting method	screwed
Mounting dimension a	88 mm
Mounting dimension b	122 mm
Mounting dimension c	7 mm
Height	110 mm
Width	150 mm
Depth	144 mm
Diameter bore	7 mm
Length bore	11 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	40 °C
Storage temperature min.	-20 °C
Storage temperature max.	80 °C
Conformity	
Product standard	EN 61558-1, EN 61558-2-4, EN 62041 category 0