

**SCREW PLUG M12 METAL**

Screw plug M12×1 mm  
Metal, hex, 1 piece

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	23111190
ECLASS-6.1	23111190
ECLASS-7.0	23111190
ECLASS-8.0	23111190
ECLASS-9.0	23111102
ECLASS-10.1	23111190
ECLASS-11.1	23111102
ECLASS-12.0	23111102
ETIM-5.0	EC000032
customs tariff number	74153300
GTIN	4048879058780
Packaging unit	1

**Installation | Connection**

Tightening torque	0,6 Nm
Mounting set	M12 x 1

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed

**Mechanical data | Material data**

Coating housing	nickel plated
Material housing	Brass

**Mechanical data | Mounting data**

Mounting method	inserted, screwed, Shaking protection
-----------------	---------------------------------------

**Environmental characteristics | Climatic**

Operating temperature min.	-100 °C
Operating temperature max.	205 °C

