

MODLINK MSDD DATA INSERT

1xSUB-D9 female/female

SUB-D9
1 × SUB-D9 (female/female)

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

| | |
|-----------------------|---------------|
| ECLASS-6.0 | 27189217 |
| ECLASS-6.1 | 27189217 |
| ECLASS-7.0 | 27189217 |
| ECLASS-8.0 | 27189217 |
| ECLASS-9.0 | 27189217 |
| ECLASS-10.1 | 27182806 |
| ECLASS-11.1 | 27182806 |
| ECLASS-12.0 | 27182806 |
| ETIM-5.0 | EC002625 |
| customs tariff number | 85366990 |
| GTIN | 4048879038065 |
| Packaging unit | 1 |

Mechanical data | Mounting data

| | |
|--------|-------|
| Height | 88 mm |
| Width | 51 mm |
| Depth | 15 mm |

Environmental characteristics | Climatic

| | |
|--------------------------|--------|
| Storage temperature min. | -30 °C |
| Storage temperature max. | 60 °C |

SUB-D9

| | |
|----------------------|------|
| Operating voltage AC | 48 V |
|----------------------|------|

| | |
|---------------------------------------|--|
| Operating voltage DC | 48 V |
| Operating voltage AC max. (UL-listed) | 30 V |
| Operating voltage DC max. (UL-listed) | 42,4 V |
| Operating current | 3 A |
| Current operating max. (UL) | 175 mA |
| Family construction form | SUB-D9 |
| Family type Back side | SUB-D9 |
| Gender | female |
| Gender Rear | female |
| Looking techniques | Standard UNC 4-40 screw thread bolt (EN 60807) |
| No. of poles | 9 |