

MODLINK MSDD DATA INSERT

1xSUB-D25 female/male + 1xSUB-D9 blind

- SUB-D25
- 1 × SUB-D25 (female/male)
- 1 × SUB-D9 (blind plug)

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27189217
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
customs tariff number	85366990
GTIN	4048879037884
Packaging unit	1
Mechanical data   Mounting data	
Height	88 mm
Width	51 mm
Depth	40 mm
Environmental characteristics   Climatic	
Storage temperature min.	-30 °C
Storage temperature max.	60 °C
SUB-D25	
Operating voltage AC	48 V

Operating voltage DC	48 V
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Operating current	3 A
Current operating max. (UL)	175 mA
Family construction form	SUB-D25
Family type Back side	SUB-D25
Gender	female
Gender Rear	male
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
No. of poles	25