

MODLINK MSDD DATA INSERT

1×USB-A fem./fem.+1×RJ45 fem./fem.+1×DVI fem./fem.

- RJ45; USB (A); DVI
- 1× RJ45, 8-pole metal, CAT5e (female/female)
 - 1× USB 2.0 (female/female) form A
 - 1× DVI (female/female)

Link to Product

Illustration



Product may differ from Image



| Commercial data | |
|--|---------------|
| ECLASS-6.0 | 27189217 |
| ECLASS-6.1 | 27189217 |
| ECLASS-7.0 | 27189217 |
| ECLASS-8.0 | 27189217 |
| ECLASS-9.0 | 27189217 |
| ECLASS-10.1 | 27182806 |
| ECLASS-11.1 | 27182806 |
| ECLASS-12.0 | 27182806 |
| ETIM-5.0 | EC002625 |
| customs tariff number | 85366990 |
| GTIN | 4048879037853 |
| Packaging unit | 1 |
| Mechanical data Mounting data | |
| Height | 88 mm |
| Width | 51 mm |
| Depth | 45 mm |
| Environmental characteristics Climatic | |
| Storage temperature min. | -10 °C |
| Storage temperature max. | 60 °C |
| USB | |

| | |
|----------------------------------|-------------------|
| Operating voltage AC | 48 V |
| Operating voltage DC | 48 V |
| Operating voltage DC (UL-listed) | 42,4 V |
| Operating current max. | 500 mA |
| USB specification | 2.0 |
| Data transmission rate max. | 480 MBit/s |
| Looking techniques | Snap-in connector |

RJ45

| | |
|---------------------------------------|-------------------|
| Operating voltage AC max. (UL-listed) | 30 V |
| Operating voltage DC max. (UL-listed) | 42,4 V |
| Current operating max. (UL) | 175 mA |
| Family construction form | RJ45 |
| Family type Back side | RJ45 |
| Cable category min. | Cat5e |
| Looking techniques | Snap-in connector |

DVI

| | |
|---------------------------|--------|
| Operating voltage AC max. | 40 V |
| Operating current max. | 1,5 A |
| Family type Back side | DVI |
| Gender | female |
| Gender Rear | female |
| No. of poles | 24 + 4 |