

**MODLINK MSDD DATA INSERT**

2xUSB-A female/female + 1xRJ45

RJ45; USB; USB (A)  
1× RJ45, 8-pole metal, CAT5e (female/female)  
2× USB (female/female) form A

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27189217
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
customs tariff number	85366990
GTIN	4048879037785
Packaging unit	1
Mechanical data   Mounting data	
Height	88 mm
Width	51 mm
Depth	60 mm
Environmental characteristics   Climatic	
Storage temperature min.	-20 °C
Storage temperature max.	60 °C
Shielding plate	
Connection information	Threaded hole M4

Tightening torque 0,9 Nm

**USB**

Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage DC (UL-listed)	42,4 V
Operating current max.	500 mA
USB specification	2.0
Data transmission rate max.	480 MBit/s
Looking techniques	Snap-in connector

**RJ45**

Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat5e
Looking techniques	Snap-in connector