

MODLINK MSDD DATA INSERT

2xUSB-A fem./fem. + 1xRJ45 + 1xSUB-D15 fem./male

- SUB-D15 HD; RJ45; USB; USB (formA)
- 1× SUB-D15 HD (female/male) VGA
- 1× RJ45, 8-pole metal, CAT5e (female/female)
- 2× USB (female/female) form A

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27189217
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
customs tariff number	85366990
GTIN	4048879037716
Packaging unit	1
Mechanical data Mounting data	
Height	88 mm
Width	51 mm
Depth	45 mm
Environmental characteristics Climatic	
Storage temperature min.	-20 °C
Storage temperature max.	60 °C
Shielding plate	

Connection information	Threaded hole M4
Tightening torque	0,9 Nm
USB	
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage DC (UL-listed)	42,4 V
Operating current max.	500 mA
USB specification	2.0
Data transmission rate max.	480 MBit/s
Looking techniques	Snap-in connector
SUB-D15	
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Operating current	3 A
Current operating max. (UL)	175 mA
Family construction form	SUB-D15
Family type Back side	SUB-D15
Gender	female
Gender Rear	male
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
No. of poles	15
RJ45	
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat5e
Looking techniques	Snap-in connector