

MODLINK MSDD DATA INSERT

2×USB-A female/female + 1×DVI

USB (form A); DVI  
2× USB (female/female) form A  
1× DVI (female/female)

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27189217
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
customs tariff number	85366990
GTIN	4048879355643
Packaging unit	1
Mechanical data   Mounting data	
Height	88 mm
Width	51 mm
Depth	45 mm
Environmental characteristics   Climatic	
Storage temperature min.	5 °C
Storage temperature max.	40 °C
Shielding plate	
Connection information	Threaded hole M4

Tightening torque 0,9 Nm

**USB**

Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage DC (UL-listed)	42,4 V
Operating current max.	500 mA
USB specification	2.0
Data transmission rate max.	480 MBit/s
Looking techniques	Snap-in connector

**DVI**

Operating voltage AC max.	40 V
Operating current max.	1,5 A
Family type Back side	DVI
Gender	female
Gender Rear	female
No. of poles	24 + 4