

**MODLINK MSDD SOCKET INSERT GERMANY**

250VAC/16A yellow

Germany (VDE) yellow  
Spring clamp terminals: max. 2× 2.5 mm² (AWG 14)

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879429603
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	41 mm

Environmental characteristics | Climatic

Storage temperature min.	-30 °C
Storage temperature max.	60 °C

Germany (VDE)

Connection cross section max.	2,5 mm²
AWG number max.	14

Operating voltage AC	250 V
Operating current	16 A
Connection	Spring clamp terminals FK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes