

**MODLINK MSDD SOCKET INSERT USA NEMA 5-15**

125VAC/15A screw connection

USA (NEMA 5-15) white  
Screw terminals

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879037273
Packaging unit	1
Mechanical data   Mounting data	
Height	88 mm
Width	51 mm
Depth	25 mm
Environmental characteristics   Climatic	
Storage temperature min.	5 °C
Storage temperature max.	40 °C
USA	
Connection cross section max.	6 mm²
AWG number max.	10

Operating voltage AC	125 V
Operating current	15 A
Connection	Screw terminals SK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes