

MODLINK MSDD SOCKET INSERT CHINA

250VAC/10A screw connection

China (CCC)
Screw terminals
with touch protection

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

| | |
|-----------------------|---------------|
| ECLASS-6.0 | 27189217 |
| ECLASS-6.1 | 27189217 |
| ECLASS-7.0 | 27189217 |
| ECLASS-8.0 | 27189217 |
| ECLASS-9.0 | 27182806 |
| ECLASS-10.1 | 27182806 |
| ECLASS-11.1 | 27182806 |
| ECLASS-12.0 | 27182806 |
| ETIM-5.0 | EC000020 |
| customs tariff number | 85366990 |
| GTIN | 4048879037266 |
| Packaging unit | 1 |

Mechanical data | Mounting data

| | |
|--------|-------|
| Height | 88 mm |
| Width | 51 mm |
| Depth | 25 mm |

Environmental characteristics | Climatic

| | |
|--------------------------|--------|
| Storage temperature min. | -30 °C |
| Storage temperature max. | 60 °C |

China (CCC)

| | |
|-------------------------------------|-------------------|
| Connection cross-section solid max. | 4 mm ² |
|-------------------------------------|-------------------|

| | |
|--|--------------------|
| Connection cross-section stranded/fine-stranded max. | 4 mm² |
| Operating voltage AC | 250 V |
| Operating current | 10 A |
| Connection | Screw terminals SK |
| No. of poles | 2 + PE |
| Connections per pole | 2 |
| Protection contact present | yes |