

MODLINK MSDD SOCKET INSERT BRAZIL

250VAC/10 A single

Brazil
Screw terminals
10 A

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879334426
Packaging unit	1

Mechanical data | Mounting data

Height	87,5 mm
Width	50,7 mm
Depth	34 mm

Environmental characteristics | Climatic

Storage temperature min.	5 °C
Storage temperature max.	35 °C

Brazil

Connection cross section max.	1,5 mm ²
-------------------------------	---------------------

AWG number max.	16
Operating voltage AC	250 V
Operating current	10 A
Connection	Screw terminals SK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes