

MODLINK MSDD SOCKET INSERT SOUTH AFRICA

250VAC/16A

South Africa
Screw terminals

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879410588
Packaging unit	1
Mechanical data Mounting data	
Height	87 mm
Width	51 mm
Depth	35 mm
Environmental characteristics Climatic	
Storage temperature min.	-10 °C
Storage temperature max.	60 °C
South Africa	
Connection cross section max.	4 mm²
AWG number max.	12

Operating voltage AC	250 V
Operating current	16 A
Connection	Screw terminals SK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes