

MODLINK MSDD SINGLE COMBI INSERT USA NEMA 5-15

1xRJ45 female/female

- 1 × NEMA 5-15 (plug-solder connection)
- 1 × RJ45, 8-pole metal, CAT5e (female/female)

Link to Product

Illustration



Product may differ from Image



| Commercial data | |
|--|---------------|
| ECLASS-6.0 | 27189217 |
| ECLASS-6.1 | 27189217 |
| ECLASS-7.0 | 27189217 |
| ECLASS-8.0 | 27189217 |
| ECLASS-9.0 | 27182806 |
| ECLASS-10.1 | 27182806 |
| ECLASS-11.1 | 27182806 |
| ECLASS-12.0 | 27182806 |
| ETIM-5.0 | EC000020 |
| customs tariff number | 85366990 |
| GTIN | 4048879037204 |
| Packaging unit | 1 |
| Mechanical data Mounting data | |
| Height | 88 mm |
| Width | 51 mm |
| Depth | 30 mm |
| Environmental characteristics Climatic | |
| Storage temperature min. | 5 °C |
| Storage temperature max. | 40 °C |
| USA | |
| Connection geometry | 4.8 x 0.5 mm |

| | |
|---------------------------------------|------------------------|
| Operating voltage AC | 125 V |
| Operating current | 15 A |
| Connection | Plug-solder connection |
| No. of poles | 2 + PE |
| Protection contact present | yes |
| RJ45 | |
| Operating voltage AC max. (UL-listed) | 30 V |
| Operating voltage DC max. (UL-listed) | 42,4 V |
| Current operating max. (UL) | 175 mA |
| Family construction form | RJ45 |
| Family type Back side | RJ45 |
| Cable category min. | Cat5e |
| Looking techniques | Snap-in connector |