

MODLINK MSDD DBL COMBI INSERT FRANCE

1xRJ45+USB-A + RCD opening

- 1 × France (UTE-NF) white
- 1 × RJ45, 8-pole metal, CAT5e (female/female)
- 1 × USB 3.0 (female/female) form A
- 1 × FI cut-out

Link to Product

Illustration



Product may differ from Image



| Commercial data | |
|--|---------------|
| ECLASS-6.0 | 27189217 |
| ECLASS-6.1 | 27189217 |
| ECLASS-7.0 | 27189217 |
| ECLASS-8.0 | 27189217 |
| ECLASS-9.0 | 27182806 |
| ECLASS-10.1 | 27182806 |
| ECLASS-11.1 | 27182806 |
| ECLASS-12.0 | 27182806 |
| ETIM-5.0 | EC000020 |
| customs tariff number | 85366990 |
| GTIN | 4048879446341 |
| Packaging unit | 1 |
| Mechanical data Mounting data | |
| Height | 88 mm |
| Width | 116 mm |
| Depth | 70 mm |
| Environmental characteristics Climatic | |
| Storage temperature min. | 5 °C |
| Storage temperature max. | 40 °C |
| Shielding plate | |

| | |
|---------------------------------------|--------------------|
| Connection information | Threaded hole M4 |
| Tightening torque | 0,9 Nm |
| France (UTE-NF) | |
| Connection cross section max. | 4 mm ² |
| AWG number max. | 12 |
| Operating voltage AC | 250 V |
| Operating current | 16 A |
| Connection | Screw terminals SK |
| No. of poles | 2 + PE |
| Connections per pole | 2 |
| Protection contact present | yes |
| USB | |
| Operating voltage AC | 48 V |
| Operating voltage DC | 48 V |
| Operating voltage AC max. (UL-listed) | 30 V |
| Operating voltage DC max. (UL-listed) | 42,4 V |
| Operating current | 1,5 A |
| USB specification | 3.0 |
| Data transmission rate max. | 5000 MBit/s |
| Looking techniques | Snap-in connector |
| RJ45 | |
| Operating voltage AC max. (UL-listed) | 30 V |
| Operating voltage DC max. (UL-listed) | 42,4 V |
| Current operating max. (UL) | 175 mA |
| Family construction form | RJ45 |
| Family type Back side | RJ45 |
| Cable category min. | Cat5e |
| Looking techniques | Snap-in connector |