

MODLINK MSDD SINGLE COMBI INSERT GREAT BRITAIN

1x RJ45 + 1x data cutout

- 1x Great Britain (BS)
- 1x RJ45, 8-pole metal, CAT6A (female/female)
- 1x RJ45 cut-out

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
customs tariff number	85366990
GTIN	4048879601023
Packaging unit	1
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data   Mounting data	
Height	87,5 mm
Width	50,7 mm
Depth	43 mm
Environmental characteristics   Climatic	
Operating temperature min.	-5 °C
Operating temperature max.	50 °C

Storage temperature min.	-10 °C
Storage temperature max.	60 °C
<b>Shielding plate</b>	
Connection information	Threaded hole M4
Tightening torque	0,9 Nm
<b>England</b>	
Operating voltage AC	250 V
Operating current	13 A
No. of poles	2 + PE
Protection contact present	yes
<b>RJ45</b>	
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat6a
Looking techniques	Snap-in connector