

MODLINK MSDD SINGLE COMBI INSERT SWISS

1x RJ45 + 1x data cutout

- 1x Swiss
- 1x RJ45, 8-pole metal, CAT6A (female/female)
- 1x RJ45 cut-out

Link to Product

Illustration



Product may differ from Image



| Commercial data | |
|--|---------------|
| ECLASS-6.0 | 27189217 |
| ECLASS-6.1 | 27189217 |
| ECLASS-7.0 | 27189217 |
| ECLASS-8.0 | 27189217 |
| ECLASS-9.0 | 27182806 |
| ECLASS-10.1 | 27182806 |
| ECLASS-11.1 | 27182806 |
| ECLASS-12.0 | 27182806 |
| ETIM-5.0 | EC002625 |
| customs tariff number | 85366990 |
| GTIN | 4048879601078 |
| Packaging unit | 1 |
| Device protection Electrical | |
| Degree of protection (EN IEC 60529) | IP20 |
| Mechanical data Mounting data | |
| Height | 87,5 mm |
| Width | 50,7 mm |
| Depth | 43 mm |
| Environmental characteristics Climatic | |
| Operating temperature min. | -5 °C |
| Operating temperature max. | 50 °C |

| | |
|--------------------------|--------|
| Storage temperature min. | -10 °C |
|--------------------------|--------|

| | |
|--------------------------|-------|
| Storage temperature max. | 60 °C |
|--------------------------|-------|

Shielding plate

| | |
|------------------------|------------------|
| Connection information | Threaded hole M4 |
|------------------------|------------------|

| | |
|-------------------|--------|
| Tightening torque | 0,9 Nm |
|-------------------|--------|

Swiss

| | |
|-------------------------------|---------------------|
| Connection cross section max. | 1,5 mm ² |
|-------------------------------|---------------------|

| | |
|-----------------|----|
| AWG number max. | 16 |
|-----------------|----|

| | |
|----------------------|-------|
| Operating voltage AC | 250 V |
|----------------------|-------|

| | |
|-------------------|------|
| Operating current | 10 A |
|-------------------|------|

| | |
|------------|---------------------------|
| Connection | Spring clamp terminals FK |
|------------|---------------------------|

| | |
|--------------|--------|
| No. of poles | 2 + PE |
|--------------|--------|

| | |
|----------------------|---|
| Connections per pole | 2 |
|----------------------|---|

| | |
|----------------------------|-----|
| Protection contact present | yes |
|----------------------------|-----|

RJ45

| | |
|---------------------------------------|------|
| Operating voltage AC max. (UL-listed) | 30 V |
|---------------------------------------|------|

| | |
|---------------------------------------|--------|
| Operating voltage DC max. (UL-listed) | 42,4 V |
|---------------------------------------|--------|

| | |
|-----------------------------|--------|
| Current operating max. (UL) | 175 mA |
|-----------------------------|--------|

| | |
|--------------------------|------|
| Family construction form | RJ45 |
|--------------------------|------|

| | |
|-----------------------|------|
| Family type Back side | RJ45 |
|-----------------------|------|

| | |
|---------------------|-------|
| Cable category min. | Cat6a |
|---------------------|-------|

| | |
|--------------------|-------------------|
| Looking techniques | Snap-in connector |
|--------------------|-------------------|