

MODLINK MSDD SINGLE COMBI INSERT INDIA

2x data cutout

1× India (white)
2× RJ45 cut-out

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879601108
Packaging unit	1
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data Mounting data	
Height	87,5 mm
Width	50,7 mm
Depth	43 mm
Environmental characteristics Climatic	
Operating temperature min.	-5 °C
Operating temperature max.	50 °C

Storage temperature min.	-10 °C
--------------------------	--------

Storage temperature max.	60 °C
--------------------------	-------

Shielding plate

Connection information	Threaded hole M4
------------------------	------------------

Tightening torque	0,9 Nm
-------------------	--------

India

Connection cross section max.	1,5 mm ²
-------------------------------	---------------------

AWG number max.	16
-----------------	----

Operating voltage AC	240 V
----------------------	-------

Operating current	5 A
-------------------	-----

Connection	Screw terminals SK
------------	--------------------

No. of poles	2 + PE
--------------	--------

Connections per pole	2
----------------------	---

Protection contact present	yes
----------------------------	-----