

Modlink MSDD-set: Frame 4000-68213-0000000,  
insert 4000-68000-0140000

Link to Product

Illustration



Product may differ from Image



| Commercial data |          |
|-----------------|----------|
| ECLASS-6.0      | 27189217 |
| ECLASS-6.1      | 27189217 |
| ECLASS-7.0      | 27189217 |
| ECLASS-8.0      | 27189217 |
| ECLASS-9.0      | 27189217 |
| ECLASS-10.1     | 27182806 |
| ECLASS-11.1     | 27182806 |
| ECLASS-12.0     | 27182806 |

|                       |               |
|-----------------------|---------------|
| ETIM-5.0              | EC002625      |
| customs tariff number | 85366990      |
| GTIN                  | 4048879033510 |
| Packaging unit        | 1             |

**Frame**

|                                               |                       |
|-----------------------------------------------|-----------------------|
| Degree of protection (EN IEC 60529)           | IP65                  |
| Operating temperature min.                    | -10 °C                |
| Operating temperature max.                    | 60 °C                 |
| Storage temperature min.                      | -25 °C                |
| Storage temperature max.                      | 60 °C                 |
| Suitable for installation wall thickness min. | 1 mm                  |
| Suitable for installation wall thickness max. | 5 mm                  |
| Coating housing                               | surface finished      |
| Color cover                                   | transparent           |
| Material lid                                  | PC                    |
| Material housing                              | Fine zinc die casting |

**Germany (VDE)**

|                               |                           |
|-------------------------------|---------------------------|
| Connection cross section max. | 2,5 mm²                   |
| AWG number max.               | 14                        |
| Operating voltage AC          | 250 V                     |
| Operating current min.        | 10 A                      |
| Operating current max.        | 16 A                      |
| Connection                    | Spring clamp terminals FK |
| No. of poles                  | 2 + PE                    |
| Connections per pole          | 2                         |
| Protection contact present    | yes                       |