

Modlink MSDD-set: Frame 4000-68223-0000000,
insert 4000-68000-0900000 + 4000-68000-0030000

Link to Product

Illustration



Product may differ from Image

**Commercial data**

| | |
|-----------------------|---------------|
| ECLASS-6.0 | 27189217 |
| ECLASS-6.1 | 27189217 |
| ECLASS-7.0 | 27189217 |
| ECLASS-8.0 | 27189217 |
| ECLASS-9.0 | 27189217 |
| ECLASS-10.1 | 27182806 |
| ECLASS-11.1 | 27182806 |
| ECLASS-12.0 | 27182806 |
| ETIM-5.0 | EC002625 |
| customs tariff number | 85366990 |
| GTIN | 4048879032643 |
| Packaging unit | 1 |

Frame

| | |
|---|-----------------------|
| Degree of protection (EN IEC 60529) | IP65 |
| Operating temperature min. | -10 °C |
| Operating temperature max. | 60 °C |
| Storage temperature min. | -25 °C |
| Storage temperature max. | 60 °C |
| Suitable for installation wall thickness min. | 1 mm |
| Suitable for installation wall thickness max. | 5 mm |
| Coating housing | surface finished |
| Color cover | transparent |
| Material lid | PC |
| Material housing | Fine zinc die casting |

USA

| | |
|----------------------------|------------------------|
| Connection geometry | 4.8 x 0.5 mm |
| Operating voltage AC | 125 V |
| Operating current | 15 A |
| Connection | Plug-solder connection |
| No. of poles | 2 + PE |
| Protection contact present | yes |

USB

| | |
|----------------------------------|-------------------|
| Operating voltage AC | 48 V |
| Operating voltage DC | 48 V |
| Operating voltage DC (UL-listed) | 42,4 V |
| Operating current max. | 500 mA |
| USB specification | 2.0 |
| Data transmission rate max. | 480 MBit/s |
| Looking techniques | Snap-in connector |