

MODLINK MSDD CABLE ENTRY SYSTEM

KDP 24/22

Size 24  
For sale only in packing units  
Cable diameter (16)× 3...6.5 mm, (4)× 5...9.2 mm, (2)× 8...12.5 mm

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27400604
ECLASS-7.0	27400604
ECLASS-8.0	27400604
ECLASS-9.0	27400604
ECLASS-10.1	27400604
ECLASS-11.1	27400604
ECLASS-12.0	27400604
ETIM-5.0	EC000211
customs tariff number	39269097
GTIN	4048879031660
Packaging unit	1
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP65
Mechanical data   Material data	
Material housing	PA
Mechanical data   Mounting data	
Height	146 mm
Width	58 mm
Depth	14 mm
Environmental characteristics   Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	70 °C