

MODLIGHT50/70 MAGNET BASE WITH M12 8-POLE

Side cable entry

Magnet base
with M12 flange plug connector (8-pole)

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27371235
ECLASS-6.1	27371235
ECLASS-7.0	27371235
ECLASS-8.0	27371235
ECLASS-9.0	27371235
ECLASS-10.1	27371235
ECLASS-11.1	27371235
ECLASS-12.0	27371235
ETIM-5.0	EC001154
customs tariff number	85319000
GTIN	4048879031080
Packaging unit	1
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Mechanical data Material data	
Color housing	black
Material housing	Aluminium
Mechanical data Mounting data	
Height	35 mm
Width	70 mm
Depth	70 mm
Connection type 2	
Family construction form	M12
Gender	male
Coding	A
No. of poles	5

PIN 1	n.c.
PIN 2	n.c.
PIN 3	0 V DC
PIN 4	24 V DC
PIN 5	FE
Family construction form	M12
Gender	male
Coding	A
No. of poles	8