

**COMLIGHT56 LED GREEN STATUS LIGHT**

Input 24VDC

Compact status light  
green

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27371220
ECLASS-6.1	27110390
ECLASS-7.0	27110390
ECLASS-8.0	27110390
ECLASS-9.0	27110350
ECLASS-10.1	27110350
ECLASS-11.1	27110350
ECLASS-12.0	27110350
ETIM-5.0	EC000232
customs tariff number	85319000
GTIN	4048879853866
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Current consumption max.	26 mA

Industrial communication | HMI

Luminous intensity	1355 mcd
--------------------	----------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

Mechanical data | Material data

Material housing                      Plastic

**Mechanical data | Mounting data**

Height	61 mm
Width	56 mm
Depth	56 mm

**Environmental characteristics | Climatic**

Operating temperature min.	-30 °C
Operating temperature max.	50 °C

**Connection type 1**

Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	2
PIN 1	24 V DC (0 V)
PIN 2	0 V (24 V DC)