

Modlight70 Pro LED modul amber

Input 24VDC

LED module (yellow)

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27371200
ECLASS-6.1	27371220
ECLASS-7.0	27371220
ECLASS-8.0	27371220
ECLASS-9.0	27371220
ECLASS-10.1	27371220
ECLASS-11.1	27371220
ECLASS-12.0	27371220
ETIM-5.0	EC000232
customs tariff number	85319000
GTIN	4048879752633
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Current consumption max.	62,5 mA
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked
Mechanical data Material data	
Material housing	PC
Mechanical data Mounting data	
Height	49 mm

Width	70 mm
Depth	70 mm
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	60 °C
Connection type 1	
Mounting method	bayonet-locking