

**Modlight70 Pro connecting modul tube mounting**

Input 24VDC

Basic for tube mounting  
Connection cables are in the online shop under "Connection Technology".

**Link to Product**

**Illustration**



Product may differ from Image



**Commercial data**

ECLASS-6.0	27371232
ECLASS-6.1	27371232
ECLASS-7.0	27371232
ECLASS-8.0	27371232
ECLASS-9.0	27371232
ECLASS-10.1	27371232
ECLASS-11.1	27371232
ECLASS-12.0	27371232
ETIM-5.0	EC001152
ETIM-6.0	EC001152
ETIM-7.0	EC001152
customs tariff number	85319000
GTIN	4048879752480
Packaging unit	1

**Electrical data | Supply**

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

**Mechanical data | Material data**

Color housing	black
Material housing	Plastic
<b>Mechanical data   Mounting data</b>	
Height	99 mm
Width	70 mm
Depth	70 mm
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-30 °C
Operating temperature max.	60 °C
<b>Connection type 1</b>	
Mounting method	bayonet-locking