

Signal tower Modlight50 Pro equipped with LED modules

green,amber,red,buzzer

Basic, buzzer, flash + LED modules  
green, yellow, red

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27371230
ECLASS-6.1	27371230
ECLASS-7.0	27371230
ECLASS-8.0	27371230
ECLASS-9.0	27371230
ECLASS-10.1	27371230
ECLASS-11.1	27371230
ECLASS-12.0	27371230
ETIM-5.0	EC001042
customs tariff number	85318070
GTIN	4048879759656
Packaging unit	1
Electrical data   Supply	
Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V
Current consumption max.	385 mA
Industrial communication   HMI	
Reduced sound pressure at 1 m	80 dB
Sound pressure at 1 m	90 dB
HMI   Illumination properties	

Blink cycles 60 ±12 per minute

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

**Mechanical data | Material data**

Color housing	black
Material housing	Plastic

**Mechanical data | Mounting data**

Height	253,5 mm
Width	50 mm
Depth	50 mm

**Environmental characteristics | Climatic**

Operating temperature min.	-30 °C
Operating temperature max.	60 °C