



M12 MV insert shielded male snap / female

Insert - mobile housing
Female straight – male straight
M12, 5-pole
A-coded
Good chemical and oil resistance (oil resistance does not apply to use with PVC cable)
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

Side 1

Family construction form	M12
Coding	A

Side 2

Family construction form	M12
Coding	A

Commercial data

ECLASS-6.0	27260702
ECLASS-6.1	27279221
ECLASS-7.0	27440104

ECLASS-8.0	27440104
ECLASS-9.0	27440106
ECLASS-10.1	27440106
ECLASS-11.1	27440106
ECLASS-12.0	27440106
ETIM-5.0	EC001855
customs tariff number	85366990
GTIN	4048879562812
Packaging unit	1

Electrical data | Supply

Operating voltage AC	49 V
Operating voltage DC	49 V
Current operating per contact max.	4 A

Installation | Connection

Tightening torque	0,6 Nm
Mounting set	M12 x 1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65, IP67
Additional condition protection degree	inserted, screwed
Rated surge voltage	1,5 kV

Mechanical data | Material data

Coating housing	nickel plated
Material gasket	FKM
Material housing	Brass

Mechanical data | Mounting data

Mounting method	inserted, screwed, Shaking protection
-----------------	---------------------------------------

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	85 °C