



Adaptor M12 female 0° X-cod. / RJ45 0°

8-pol., shielded, CAT6A


Adapter
M12 – RJ45
Female straight – female straight
8-pole
X-coded
Gigabit
Ethernet CAT6A
shielded
Cap nut

Link to Product

Illustration



Product may differ from Image



Side 1

Family construction form	M12
Coding	X

Commercial data

ECLASS-6.0	27143423
ECLASS-6.1	27279221
ECLASS-7.0	27440104

ECLASS-8.0	27440104
ECLASS-9.0	27440106
ECLASS-10.1	27440106
ECLASS-11.1	27440106
ECLASS-12.0	27440106
ETIM-5.0	EC002640
customs tariff number	85366990
GTIN	4048879699402
Packaging unit	1

Electrical data | Supply

Operating current max.	1,75 A
------------------------	--------

Industrial communication

Supported protocol	Ethernet
Transfer parameters	CAT6A

Installation | Connection

Width across flats	SW18
--------------------	------

Important installation notes

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.