

| | |
|-----------------|---------------|
| Coating housing | powder-coated |
|-----------------|---------------|

| | |
|-----------------|----------|
| Coating locking | verzinkt |
|-----------------|----------|

| | |
|-----------------|-----|
| Material gasket | NBR |
|-----------------|-----|

| | |
|------------------|----------------------|
| Material housing | Aluminum die casting |
|------------------|----------------------|

| | |
|------------------|-------|
| Locking material | Steel |
|------------------|-------|

Mechanical data | Mounting data

| | |
|------|-----|
| Size | B10 |
|------|-----|

| | |
|--------|---------|
| Height | 72,5 mm |
|--------|---------|

| | |
|-------|-------|
| Width | 43 mm |
|-------|-------|

| | |
|-------|--------|
| Depth | 114 mm |
|-------|--------|

| | |
|--------------------|----------------------|
| Looking techniques | Double locking lever |
|--------------------|----------------------|

Environmental characteristics | Climatic

| | |
|----------------------------|--------|
| Operating temperature min. | -40 °C |
|----------------------------|--------|

| | |
|----------------------------|--------|
| Operating temperature max. | 100 °C |
|----------------------------|--------|

| | |
|------------------------------------|-----------|
| Climatic category (EN IEC 60068-1) | 40/100/21 |
|------------------------------------|-----------|