


B10 frame (male) for 3 modules

A...C


B10
Frame
Male
for 3 modules
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27143424
ECLASS-6.1	27261209
ECLASS-7.0	27440206
ECLASS-8.0	27440206
ECLASS-9.0	27440206
ECLASS-10.1	27440206
ECLASS-11.1	27440206
ECLASS-12.0	27440206
ETIM-5.0	EC002312
customs tariff number	85389099
GTIN	4048879641760
Packaging unit	1

Installation

Connection cross section min.	1 mm ²
Connection cross section max.	6 mm ²
AWG number min.	18
AWG number max.	10

Installation | Connection

Connection	Screw terminals SK
Insertion cycles safety element min.	20
Mating cycles min.	500

Installation | Pin assignment

No. of poles	2 + PE
--------------	--------

Mechanical data	
Holding force modules (insert) min.	300 N
Holding force modules (pull) min.	600 N
Holding force PE contact	250 N
Frame type	male
Pulling force max.	60 N
Mechanical data Material data	
Coating housing	nickel plated
Coating contact	nickel plated
Combustibility class (UL94)	V-0
Material housing	Zinc die-casting
Material contact	Brass
Material safety element	PC GF
Mechanical data Mounting data	
Number of module slots	3
Size	B10
Height	36,5 mm
Width	34,4 mm
Depth	64,2 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	125 °C
Climatic category (EN IEC 60068-1)	40/125/10