

1,6 mm crimp contact m/turned/silver/0,75-1 mm²

100 pieces

Turned crimp contact

Male

1.6 mm

0.75...1 mm² (AWG 18)

Quantity: 100 pcs.

Technical data will be only guaranteed with Murrelektronik components.

[Link to Product](#)**Illustration**

Product may differ from Image

Commercial data

ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
GTIN	4048879649841
Packaging unit	100

Installation

Connection cross section min.	0,75 mm ²
Connection cross section max.	1 mm ²
AWG number max.	18

Installation | Connection

Stripping length	7 mm
Connection	Crimp
Gender	male
Mating cycles min.	500

Mechanical data | Material data

Coating contact	silver-plated
-----------------	---------------

Mechanical data Mounting data	
Height	3,2 mm
Width	3,2 mm
Depth	25 mm