

1,6 mm crimp contact f/turned/gold/0,75-1 mm²

100 pieces

Turned crimp contact  
Female  
1.6 mm  
0.75...1 mm² (AWG 18)  
Quantity: 100 pcs.  
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
GTIN	4048879653589
Packaging unit	100
Installation	
Connection cross section min.	0,75 mm²
Connection cross section max.	1 mm²
AWG number max.	18
Installation   Connection	
Stripping length	7 mm
Connection	Crimp
Gender	female
Mating cycles min.	500
Mechanical data   Material data	
Coating contact	gold plated

Mechanical data   Mounting data	
Height	3,5 mm
Width	3,5 mm
Depth	21,6 mm

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | [shop@murrinc.com](mailto:shop@murrinc.com) | [shop.murrinc.com](http://shop.murrinc.com)