

4 mm crimp contact f/turned/silver/1,5 mm²

100 pieces

Turned crimp contact
Female
4 mm
1.5 mm² (AWG 16)
Quantity: 100 pcs.
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
GTIN	4048879653763
Packaging unit	100
Installation	
Connection cross section max.	1,5 mm²
AWG number max.	16
Installation Connection	
Stripping length	9 mm
Connection	Crimp
Gender	female
Mating cycles min.	500
Mechanical data Material data	
Coating contact	silver-plated

Brass

Height	6 mm
Width	6 mm
Depth	23,3 mm

Depth	23,3 mm
-------	---------