

4 mm crimp contact f/turned/silver/6 mm²

100 pieces

Turned crimp contact

Female

4 mm

6 mm² (AWG 10)

Quantity: 100 pcs.

Technical data will be only guaranteed with Murrelektronik components.

[Link to Product](#)**Illustration**

Product may differ from Image

Commercial data

ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
GTIN	4048879653794
Packaging unit	100

Installation

Connection cross section max.	6 mm ²
AWG number max.	10

Installation | Connection

Stripping length	9 mm
Connection	Crimp
Gender	female
Mating cycles min.	500

Mechanical data | Material data

Coating contact	silver-plated
-----------------	---------------

Brass

Height	6 mm
Width	6 mm
Depth	23,3 mm

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com