

Coax insert 75Ohm (female)

Coax insert
Female
1-pole
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000438
customs tariff number	85389099
GTIN	4048879649490
Packaging unit	1
Electrical data	
Insertion loss max.	1 dB
Electrical data Supply	
Operating voltage AC	50 V
Operating voltage DC	50 V
Operating current	16 A
Industrial communication HMI	
Return loss min.	20 dB
Installation	
Connection cross section min.	0,14 mm²
Connection cross section max.	2,5 mm²
AWG number min.	26
AWG number max.	13
Installation Connection	

Wire insulation diameter min.	9,5 mm
Connection	Crimp
Gender	female
Mating cycles min.	500

Installation | Pin assignment

No. of poles	1
--------------	---

Device protection | Electrical

Pollution Degree	3
Rated surge voltage	0,8 kV
Insulation resistance min.	100 MΩ
Overvoltage category (EN 60664-1)	I
Overvoltage category (EN 60950-1)	III

Mechanical data | Material data

Combustibility class (UL94)	V-0
Material housing	PA

Mechanical data | Mounting data

Height	20,3 mm
Width	16,7 mm
Depth	45,6 mm

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	125 °C
Climatic category (EN IEC 60068-1)	40/125/10