

GigaBit crimp contact - M, 0,2-0,5 mm²

GigaBit crimp contact - M, 0,2-0,5 mm²


Turned crimp contact

Male

Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27261204
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
GTIN	4048879672887
Packaging unit	100
Installation	
Connection cross section min.	0,2 mm²
Connection cross section max.	0,5 mm²
AWG number min.	24
AWG number max.	20
Installation Connection	
Stripping length	4,2 mm
Connection	Crimp
Gender	male
Mating cycles min.	200
Mechanical data Material data	
Coating contact	gold plated
Material contact	Copper alloy